


ZONO™ SC 1 Single Door Cabinet



For recessed or side wall installation guides, please visit:
zonoinstallationguides.com



YOUR TRUSTED PARTNER IN DISINFECTING+ & SANITIZING*

- EFFECTIVE** The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals.
- SIMPLE** The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are ready to use immediately, with no rinsing, wiping, or worry.
- SAFETY FEATURES** Numerous safety features exist to provide protection during operation:
- Emergency stop buttons inside and outside
 - Clear safety glass panel doors
 - Password protected digital display panel
 - Ozone sensors
 - Magnetic door lock
 - Ozone rated door gaskets
- SUSTAINABLE**
- The ZONO™ Cabinet uses less than three cents of electricity per cycle
 - The ZONO™ Cabinet uses less than one ounce of distilled water per cycle

KILLS 99.9% OF COMMON VIRUSES+ & BACTERIA* IN 38 MINUTES (Tested by Certified Independent Laboratories)

- ✓ Norovirus
- ✓ Influenza-A
- ✓ Respiratory Syncytial Virus (RSV)
- ✓ Staphylococcus aureus (Staph)
- ✓ Methicillin-Resistant Staphylococcus aureus (MRSA)
- ✓ Escherichia coli (E. coli)
- ✓ Streptococcus pyogenes (S. pyogenes)
- ✓ Shigella dysenteriae (Shigella)
- ✓ Salmonella enteritidis (Salmonella)
- ✓ Pseudomonas aeruginosa (P. aeruginosa)

SPECIFICATIONS

- Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.
- Exterior meets ASTM C1055 standards. Safe to touch during operation.
- Dimensions: 76 3/16" H x 26 1/2" W x 31 3/16" D.
- Capacity: 28.4 cu ft.
- Weight: 131 lbs.
- No downtime between cycles.
- Use NEMA 5-15R 120V Receptacle, like an ordinary household outlet.
- Sanitizing Cycle Max Watts: 306
- Proudly made in the USA in a U.S. EPA registered facility.



Use NEMA 5-15R 120V Receptacle, like an ordinary household outlet. Optimum if located 36" AFF.

EASE OF USE FEATURES

- ERGONOMIC** The Integrated Mobile Cart System alleviates the need for bending and lifting.
- FAST** Cycles last only 38 minutes. No delay between cycles.
- POWER** No hardwiring, only requires plug-in electrical outlet.
- OPERATION** Simple operating panel.
- GUARANTEE** Includes a three-year warranty for parts and labor.

OTHER MODELS AVAILABLE

SC 1 WH Optional heat cycle to kill lice, bedbugs, and their eggs (125°F).

ACCESSORIES

RR 7 7-bin Cart **RR 10** 10-bin Cart **MC 8** 8-mat Cart **4S UC** 4-shelf Utility Cart

+Disinfecting level (kills 99.9%): Norovirus, Influenza-A, and Respiratory Syncytial Virus on non-porous surfaces.

*Sanitizing level (kills 99.9%): Staphylococcus aureus, Methicillin-Resistant Staphylococcus aureus, Escherichia Coli, Streptococcus Pyogenes, Shigella dysenteriae, Salmonella Enteritidis, and Pseudomonas Aeruginosa on non-porous, semi-porous and porous surfaces.

•Less than three cents of electricity is based on a standard disinfect and sanitize cycle for the SC1 ZONO™ Cabinet using an energy cost of 17.5 cents per kilowatt hour. SC1 ZONO™ Cabinet with optional Heat uses thirty-nine cents of electricity per 90-minute cycle.

••Less than one ounce of water per cycle is based on a standard disinfect and sanitize cycle for the SC1 ZONO™ Cabinet.