3343 Peachtree Rd. Suite #180 - 1303 • Atlanta, GA 30326 • 770-212-9201 www.zonotechnologies.com

Double Door Double Deep Cabinet ZONO™ SC 2 DD



For recessed or side wall installation guides, please visit: zonoinstallationguides.com



YOUR TRUSTED PARTNER IN DISINFECTING* & SANITIZING*

The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different **EFFECTIVE**

surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals.

The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto **SIMPLE**

the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are

ready to use immediately, with no rinsing, wiping, or worry.

SAFETY Numerous safety features exist to provide protection during operation: **FEATURES**

• Emergency stop buttons inside and outside

 Clear safety glass panel doors Magnetic door lock Password protected digital display panel • Ozone rated door gaskets

SUSTAINABLE • The ZONO™ Cabinet uses four cents of electricity per cycle•

• The ZONO™ Cabinet uses 1.2 ounces of distilled water per cycle"

KILLS 99.9% OF COMMON VIRUSES* & BACTERIA* IN 38 MINUTES (Tested by Certified Independent Laboratories)

✓ Norovirus

✓ Respiratory Syncytial Virus (RSV)

✓ Staphylococcus aureus (Staph)

✓ Influenza-A ✓ Streptococcus pyogenes (S. pyogenes)

> ✓ Shigella dysenteriae (Shigella) ✓ Salmonella enteritidis (Salmonella)

✓ Escherichia coli (E. coli)

Ozone sensors

✓ Methicillin-Resistant Staphylococcus aureus (MRSA) ✓ Pseudomonas aeruginosa (P. aeruginosa)

SPECIFICATIONS

Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.

Exterior meets ASTM C1055 standards. Safe to touch during operation.

Dimensions: 76 3/16" H x 52 5/8" W x 58 9/16" D.

Capacity: 113.6 cu ft.

Weight: 474 lbs.

No downtime between cycles.

Requires NEMA 5-20R 120V Receptacle on Dedicated 20A Circuit.

Sanitizing Cycle Max Watts: 800

• Proudly made in the USA in a U.S. EPA registered facility.



120V Receptacle.
Optimum if located 36" AFF.

EASE OF USE FEATURES

ERGONOMIC The Integrated Mobile Cart System alleviates the need for bending and lifting.

FAST Sanitizing cycles last only 38 minutes. No delay between cycles.

POWER No hardwiring, only requires plug-in electrical outlet.

OPERATION Simple operating panel.

GUARANTEE Includes a three-year warranty for parts and labor.

OTHER MODELS AVAILABLE

SC 2 DD WH Heat cycle kills lice, bedbugs, and their eggs (125°F).

Drying cycle dries damp or wet apparel and gear without damage. SC 2 DD WD

ACCESSORIES

HC 3M 48 Helmet Cart 4S UC 4-shelf Utility Cart 4S D UC 4-shelf Deep Utility Cart **RR 10** 10-bin Cart

PC 2M 22 Pad Cart **GC** Garment Cart SD 16 Shoe Dryer



ZONO Technologies™ www.zonotechnologies.com 770.212.9201









*Sanitizing level (kills 99.9%): Staphylococcus aureus, Methicillin-Resistant Staphylococcus aureus, Escherichia Coli, Streptococcus Pyogenes, Shigella dysenteriae, Salmonella Enteritidis, and Pseudomonas Aeruginosa on non-porous, semi-porous and porous surfaces

•Four cents of electricity is based on a standard disinfect and sanitize cycle for the SC2 DD ZONO™ Cabinet using an energy cost of 17.5 cents per kilowatt hour. SC2 DD ZONO™ Cabinet with optional Heat uses eighty cents of electricity per 90-minute cycle and the Dry cycle uses eighty cents of electricity per 90-minute cycle

using an energy cost of 17.5 cents per kilowatt hour. ••1.2 ounces of water per cycle is based on a standard disinfect and sanitize cycle for the SC2 DD ZONO™ Cabinet.