

ZONO™ SC 2 DD WH Double Door Double Deep Cabinet with Heat



For recessed or side wall installation guides, please visit:
zonoinstallationguides.com



YOUR TRUSTED PARTNER IN DISINFECTING* & SANITIZING*

- EFFECTIVE** The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals.
- SIMPLE** The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are ready to use immediately, with no rinsing, wiping, or worry.
- SAFETY FEATURES** Numerous safety features exist to provide protection during operation:
 - Emergency stop buttons inside and outside
 - Clear safety glass panel doors
 - Password protected digital display panel
 - Ozone sensors
 - Magnetic door lock
 - Ozone rated door gaskets
- SUSTAINABLE**
 - The ZONO™ Cabinet uses four cents of electricity per cycle*
 - The ZONO™ Cabinet uses 1.2 ounces of distilled water per cycle**

KILLS 99.9% OF COMMON VIRUSES* & BACTERIA* IN 38 MINUTES (Tested by Certified Independent Laboratories)

- ✓ Norovirus
- ✓ Influenza-A
- ✓ Respiratory Syncytial Virus (RSV)
- ✓ Staphylococcus aureus (Staph)
- ✓ Methicillin-Resistant Staphylococcus aureus (MRSA)
- ✓ Escherichia coli (E. coli)
- ✓ Streptococcus pyogenes (S. pyogenes)
- ✓ Shigella dysenteriae (Shigella)
- ✓ Salmonella enteritidis (Salmonella)
- ✓ Pseudomonas aeruginosa (P. aeruginosa)

SPECIFICATIONS

- Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.
- Heat cycle kills lice, bedbugs, and their eggs (125°F).
- Exterior meets ASTM C1055 standards. Safe to touch during operation.
- Dimensions: 76 3/16" H x 52 5/8" W x 62" D.
- Capacity: 113.6 cu ft. | Weight: 496 lbs.
- Max Watts: Sanitizing Cycle 800 | Heat Cycle 3200
- No downtime between cycles.
- Requires NEMA 14-30R 240V Receptacle on Dedicated 30A 2 Phase Circuit.
- Proudly made in the USA in a U.S. EPA registered facility.



Use NEMA 14-30R 240V Receptacle. When running heat cycle, requires dedicated 30A 2 Phase Circuit. Optimum if located 36" AFF.

EASE OF USE FEATURES

- ERGONOMIC** The Integrated Mobile Cart System alleviates the need for bending and lifting.
- FAST** Sanitizing cycles last only 38 minutes. No delay between cycles.
- HEAT** Heat cycles lasts 90 minutes. Items can be removed immediately. Cool down may be required before starting next cycle.
- POWER** No hardwiring, only requires plug-in electrical outlet.
- OPERATION** Simple operating panel.
- GUARANTEE** Includes a three-year warranty for parts and labor.

OTHER MODELS AVAILABLE

- SC 2 DD** Without optional heat cycle.
- SC 2 DD WD** Drying cycle dries damp or wet apparel and gear without damage.

ACCESSORIES

- RR 10** 10-bin Cart
- HC 3M 48** Helmet Cart
- 4S UC** 4-shelf Utility Cart
- 4S D UC** 4-shelf Deep Utility Cart
- PC 2M 22** Pad Cart
- GC** Garment Cart
- SD 16** Shoe Dryer

*Disinfecting level (kills 99.9%): Norovirus, Influenza-A, and Respiratory Syncytial Virus on non-porous surfaces.

**Sanitizing level (kills 99.9%): Staphylococcus aureus, Methicillin-Resistant Staphylococcus aureus, Escherichia Coli, Streptococcus Pyogenes, Shigella dysenteriae, Salmonella Enteritidis, and Pseudomonas Aeruginosa on non-porous, semi-porous and porous surfaces.

•Four cents of electricity is based on a standard disinfect and sanitize cycle for the SC2 DD ZONO™ Cabinet using an energy cost of 17.5 cents per kilowatt hour. SC2 DD ZONO™ Cabinet with optional Heat use eighty cents of electricity per 90-minute cycle using an energy cost of 17.5 cents per kilowatt hour.

••1.2 ounces of water per cycle is based on a standard disinfect and sanitize cycle for the SC2 DD ZONO™ Cabinet.