


ZONO™ SC 2 WD Double Door Cabinet with Drying



For recessed or side wall installation guides, please visit:
zonoinstallationguides.com

YOUR TRUSTED PARTNER IN DISINFECTING+ & SANITIZING*

- EFFECTIVE** The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals.
- SIMPLE** The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are ready to use immediately, with no rinsing, wiping, or worry.
- SAFETY FEATURES** Numerous safety features exist to provide protection during operation:
- Emergency stop buttons inside and outside
 - Clear safety glass panel doors
 - Password protected digital display panel
 - Ozone sensors
 - Magnetic door lock
 - Ozone rated door gaskets
- SUSTAINABLE**
- The ZONO™ Cabinet uses less than three cents of electricity per cycle
 - The ZONO™ Cabinet uses less than one ounce of distilled water per cycle

KILLS 99.9% OF COMMON VIRUSES+ & BACTERIA* IN 38 MINUTES (Tested by Certified Independent Laboratories)

- ✓ Norovirus
- ✓ Influenza-A
- ✓ Respiratory Syncytial Virus (RSV)
- ✓ Staphylococcus aureus (Staph)
- ✓ Methicillin-Resistant Staphylococcus aureus (MRSA)
- ✓ Escherichia coli (E. coli)
- ✓ Streptococcus pyogenes (S. pyogenes)
- ✓ Shigella dysenteriae (Shigella)
- ✓ Salmonella enteritidis (Salmonella)
- ✓ Pseudomonas aeruginosa (P. aeruginosa)

SPECIFICATIONS

- Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.
- Drying cycle dries damp apparel and gear without damage. Heat cycle to kill bed bugs, lice, and eggs.
- Exterior meets ASTM C1055 standards.
- Operates at room temperature. Safe to touch during operation.
- Outer Dimensions: 80" H x 52 5/8" W x 31 1/16" D.
- Interior Dimensions: 60" H x 48 1/2" W x 25 1/4" D.
- Capacity: 58.8 cu ft. | Weight: 284 lbs.
- Max Watts: Sanitizing Cycle 306 | Dry Cycle 1518 | Heat Cycle 1440
- No downtime between cycles.
- Requires NEMA 5-20R 120V Receptacle on Dedicated 20A Circuit.
- Access to the rear of the machine is required for electrical to plug into the building's receptacle.
- Proudly made in the USA in a U.S. EPA registered facility.



Use NEMA 5-20R 120V Receptacle.
 When running dry cycle, requires dedicated 20A Circuit. Optimum if located 36" AFF.

EASE OF USE FEATURES

- ERGONOMIC** The Integrated Mobile Cart System alleviates the need for bending and lifting.
- FAST** Sanitizing cycles last only 38 minutes. No delay between cycles.
- DRY / HEAT** Dry and Heat cycles lasts 90 minutes. Items can be removed immediately. Cool down may be required before starting heat next cycle.
- POWER OPERATION** No hardwiring, only requires plug-in electrical outlet. Simple operating panel.
- GUARANTEE** Includes a three-year warranty for parts and labor.

OTHER MODELS AVAILABLE

- SC 2** Without optional drying cycle.
- SC 2 WH** Heat cycle kills lice, bedbugs, and their eggs (125°F).

ACCESSORIES

- RR 7** 7-bin Cart **SD 16** Shoe Drying Cart **HC 3M 48** Helmet Cart **4S UC** 4-shelf Utility Cart
- RR 10** 10-bin Cart **PC 2M 22** Pad Cart **GC** Garment Cart **4S D UC** 4-shelf Deep Utility Cart

