


ZONO™ SC 1 3D Single Door Triple Deep Cabinet



On-site Assembly Required
For recessed or side wall installation
guides, please visit:
zonoinstallationguides.com



YOUR TRUSTED PARTNER IN DISINFECTING* & SANITIZING*

EFFECTIVE

The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals. Accommodates up to a queen size mattress. Suitable for FDA Class 1 exempt medical devices.

SIMPLE

The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 40 minutes, items are ready to use immediately, with no rinsing, wiping, or worry.

SAFETY FEATURES

Numerous safety features exist to provide protection during operation:

- Emergency stop buttons inside and outside
- Clear safety glass panel door
- Password protected digital display panel
- Ozone sensors
- Magnetic door lock
- Ozone rated door gaskets

SUSTAINABLE

- The ZONO™ Cabinet uses four cents of electricity per cycle
- The ZONO™ Cabinet uses less than one ounce of distilled water per cycle

KILLS 99.9% OF COMMON VIRUSES* & BACTERIA* IN 40 MINUTES (Tested by Certified Independent Laboratories)

- ✓ Measles
- ✓ Norovirus
- ✓ Influenza-A
- ✓ Respiratory Syncytial Virus (RSV)
- ✓ Staphylococcus aureus (Staph)
- ✓ Methicillin-Resistant Staphylococcus aureus (MRSA)
- ✓ Escherichia coli (E. Coli)
- ✓ Streptococcus pyogenes (Strep)
- ✓ Shigella dysenteriae (Shigella)
- ✓ Salmonella enteritidis (Salmonella)
- ✓ Pseudomonas aeruginosa (Pseudomonas)

SPECIFICATIONS

- Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.
- **On-site Assembly Required:** Ships and arrives in two (2) sections that bolt together at your placement of use. Onsite caulking at the seam required.
- Operates at room temperature. Safe to touch during operation.
- Outer Dimensions: 76 1/8" H x 26 1/2" W x 90 5/8" D.
- Interior Dimensions: 60" H x 22" W x 84" D.
- Capacity: 75 cu ft. | Weight: 385 lbs.
- Door hinges on the right side. Not field-reversible.
- Requires NEMA 5-20R 120V Receptacle on Dedicated 20A Circuit.
- Access to the rear of the machine is required for electrical to plug into the building's receptacle.
- Sanitizing Cycle Max Watts: 505
- Proudly made in the USA in a U.S. EPA registered facility.



Requires NEMA 5-20R
120V Receptacle.
Optimum if located 36" AFF.

EASE OF USE FEATURES

ERGONOMIC

The Integrated Mobile Cart System alleviates the need for bending and lifting.

FAST

Sanitizing cycle lasts only 40 minutes. No delay between cycles.

POWER

No hardwiring, only requires plug-in electrical outlet.

OPERATION

Digital display panel provides one source of control for the ZONO™ Cabinet.

GUARANTEE

Includes a three-year warranty for parts and labor.

OTHER MODELS AVAILABLE

SC 1 3D WH

Optional heat cycle to kill lice, bedbugs, and their eggs (125°F).

ACCESSORIES

RR 7 7-bin Cart

MC 8 8-mat Cart

4S UC 4-shelf Utility Cart

IGC Industrial Garment Cart

