

ZONO™ SC 1 Single Door Cabinet



For recessed or side wall installation guides, please visit:
zonoinstallationguides.com



YOUR TRUSTED PARTNER IN DISINFECTING* & SANITIZING*

- | | |
|------------------------|---|
| EFFECTIVE | The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals. |
| SIMPLE | The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are ready to use immediately, with no rinsing, wiping, or worry. |
| SAFETY FEATURES | Numerous safety features exist to provide protection during operation: <ul style="list-style-type: none"> • Emergency stop buttons inside and outside • Clear safety glass panel doors • Password protected digital display panel • Ozone sensors • Magnetic door lock • Ozone rated door gaskets |
| SUSTAINABLE | <ul style="list-style-type: none"> • The ZONO™ Cabinet uses less than three cents of electricity per cycle • The ZONO™ Cabinet uses less than one ounce of distilled water per cycle |

KILLS 99.9% OF COMMON VIRUSES* & BACTERIA* IN 38 MINUTES (Tested by Certified Independent Laboratories)

- | | |
|--|--|
| ✓ Measles | ✓ Escherichia Coli (E. Coli) |
| ✓ Norovirus | ✓ Streptococcus pyogenes (Staph) |
| ✓ Influenza-A | ✓ Shigella dysenteriae (Shigella) |
| ✓ Respiratory Syncytial Virus (RSV) | ✓ Salmonella enteritidis (Salmonella) |
| ✓ Staphylococcus aureus (Staph) | ✓ Pseudomonas aeruginosa (Pseudomonas) |
| ✓ Methicillin-Resistant Staphylococcus aureus (MRSA) | |

SPECIFICATIONS

- Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.
- Exterior meets ASTM C1055 standards.
- Operates at room temperature. Safe to touch during operation.
- Outer Dimensions: 76 3/16" H x 26 1/2" W x 31 3/16" D | Interior Dimensions: 60" H x 23" W x 26" D
- Capacity: 28.4 cu ft. | Weight: 131 lbs.
- Door hinges on the right side. Not field-reversible.
- No downtime between cycles.
- Use NEMA 5-15R 120V Receptacle, like an ordinary household outlet.
- Access to the rear of the machine is required for electrical to plug into the building's receptacle.
- Sanitizing Cycle Max Watts: 306
- Proudly made in the USA in a U.S. EPA registered facility.



Use NEMA 5-15R 120V Receptacle, like an ordinary household outlet. Optimum if located 36" AFF.

EASE OF USE FEATURES

- | | |
|------------------|--|
| ERGONOMIC | The Integrated Mobile Cart System alleviates the need for bending and lifting. |
| FAST | Cycles last only 38 minutes. No delay between cycles. |
| POWER | No hardwiring, only requires plug-in electrical outlet. |
| OPERATION | Digital display panel provides one source of control for the ZONO™ Cabinet. |
| GUARANTEE | Includes a three-year warranty for parts and labor. |

OTHER MODELS AVAILABLE

- SC 1 WH** Optional heat cycle to kill lice, bedbugs, and their eggs (125°F).

ACCESSORIES

- RR 7** 7-bin Cart **MC 8** 8-mat Cart **4S UC** 4-shelf Utility Cart