

ZONO™ SC 1 WH Single Door Cabinet with Heat



For recessed or side wall installation guides, please visit:
zonoinstallationguides.com



Heat unit addition plugs into the internal electrical receptacle located at the top of the ZONO™.



YOUR TRUSTED PARTNER IN DISINFECTING* & SANITIZING*

EFFECTIVE

The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals.

SIMPLE

The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are ready to use immediately, with no rinsing, wiping, or worry.

SAFETY FEATURES

Numerous safety features exist to provide protection during operation:

- Emergency stop buttons inside and outside
- Clear safety glass panel doors
- Password protected digital display panel
- Ozone sensors
- Magnetic door lock
- Ozone rated door gaskets

SUSTAINABLE

- The ZONO™ Cabinet uses less than three cents of electricity per cycle
- The ZONO™ Cabinet uses less than one ounce of distilled water per cycle

KILLS 99.9% OF COMMON VIRUSES* & BACTERIA* IN 38 MINUTES

(Tested by Certified Independent Laboratories)

- ✓ Measles
- ✓ Norovirus
- ✓ Influenza-A
- ✓ Respiratory Syncytial Virus (RSV)
- ✓ Staphylococcus aureus (Staph)
- ✓ Methicillin-Resistant Staphylococcus aureus (MRSA)
- ✓ Escherichia coli (E. Coli)
- ✓ Streptococcus pyogenes (Strep)
- ✓ Shigella dysenteriae (Shigella)
- ✓ Salmonella enteritidis (Salmonella)
- ✓ Pseudomonas aeruginosa (Pseudomonas)

SPECIFICATIONS

- Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.
- Heat cycle kills lice, bedbugs, and their eggs (125°F).
- Exterior meets ASTM C1055 standards.
- Operates at room temperature. Safe to touch during operation.
- Outer Dimensions: 76 3/16" H x 26 1/2" W x 31 3/16" D | Interior: 60" H x 23" W x 26" D
- Capacity: 28.4 cu ft. | Weight: 151 lbs.
- Door hinges on the right side. Not field-reversible.
- Max Watts: Sanitizing Cycle 306 | Heat Cycle 1440
- No downtime between cycles.
- Use NEMA 5-15R 120V Receptacle, like an ordinary household outlet. Requires dedicated 15A Circuit.
- Access to the rear of the machine is required for electrical to plug into the building's receptacle.
- Proudly made in the USA in a U.S. EPA registered facility.



Use NEMA 5-15R 120V Receptacle, like an ordinary household outlet.
When running heat cycle, requires dedicated 15A Circuit. Optimum if located 36" AFF.

EASE OF USE FEATURES

ERGONOMIC

The Integrated Mobile Cart System alleviates the need for bending and lifting.

FAST

Sanitizing cycles last only 38 minutes. No delay between cycles.

HEAT

Heat cycles lasts 90 minutes. Items can be removed immediately. Cool down may be required before starting next cycle.

POWER

No hardwiring, only requires plug-in electrical outlet.

OPERATION

Digital display panel provides one source of control for the ZONO™ Cabinet.

GUARANTEE

Includes a three-year warranty for parts and labor.

OTHER MODELS AVAILABLE

SC 1 Without optional heat cycle.

ACCESSORIES

RR 7 7-bin Cart

MC 8 8-mat Cart

4S UC 4-shelf Utility Cart