

## ZONO™ SC 2 DD Double Door Double Deep Cabinet



**On-site Assembly Required**  
For recessed or side wall installation  
guides, please visit:  
[zonoinstallationguides.com](http://zonoinstallationguides.com)



### YOUR TRUSTED PARTNER IN DISINFECTING\* & SANITIZING\*

- |                        |                                                                                                                                                                                                                                                                                                                                                               |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>EFFECTIVE</b>       | The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals.                                                                                                                                |
| <b>SIMPLE</b>          | The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are ready to use immediately, with no rinsing, wiping, or worry.                                                               |
| <b>SAFETY FEATURES</b> | Numerous safety features exist to provide protection during operation: <ul style="list-style-type: none"> <li>• Emergency stop buttons inside and outside</li> <li>• Clear safety glass panel doors</li> <li>• Password protected digital display panel</li> <li>• Ozone sensors</li> <li>• Magnetic door lock</li> <li>• Ozone rated door gaskets</li> </ul> |
| <b>SUSTAINABLE</b>     | <ul style="list-style-type: none"> <li>• The ZONO™ Cabinet uses four cents of electricity per cycle</li> <li>• The ZONO™ Cabinet uses 1.2 ounces of distilled water per cycle</li> </ul>                                                                                                                                                                      |

### KILLS 99.9% OF COMMON VIRUSES\* & BACTERIA\* IN 38 MINUTES

(Tested by Certified Independent Laboratories)

- |                                                      |                                        |
|------------------------------------------------------|----------------------------------------|
| ✓ Measles                                            | ✓ Escherichia coli (E. Coli)           |
| ✓ Norovirus                                          | ✓ Streptococcus pyogenes (Strep)       |
| ✓ Influenza-A                                        | ✓ Shigella dysenteriae (Shigella)      |
| ✓ Respiratory Syncytial Virus (RSV)                  | ✓ Salmonella enteritidis (Salmonella)  |
| ✓ Staphylococcus aureus (Staph)                      | ✓ Pseudomonas aeruginosa (Pseudomonas) |
| ✓ Methicillin-Resistant Staphylococcus aureus (MRSA) |                                        |

### SPECIFICATIONS

- Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.
- **On-site Assembly Required:** Ships and arrives in two (2) sections that bolt together at your placement of use. Onsite caulking at the seam required.
- Exterior meets ASTM C1055 standards. Safe to touch during operation.
- Outer Dimensions: 76 3/16" H x 52 5/8" W x 62" D | Interior: 60" H x 48 1/2" W x 52 3/8" D
- Capacity: 113.6 cu ft. | Weight: 474 lbs.
- No downtime between cycles.
- Requires NEMA 5-20R 120V Receptacle on Dedicated 20A Circuit.
- Access to the rear of the machine is required for electrical to plug into the building's receptacle.
- Sanitizing Cycle Max Watts: 800
- Proudly made in the USA in a U.S. EPA registered facility.



Use NEMA 5-20R  
120V Receptacle.  
Optimum if located 36" AFF.

### EASE OF USE FEATURES

- |                  |                                                                                |
|------------------|--------------------------------------------------------------------------------|
| <b>ERGONOMIC</b> | The Integrated Mobile Cart System alleviates the need for bending and lifting. |
| <b>FAST</b>      | Sanitizing cycles last only 38 minutes. No delay between cycles.               |
| <b>POWER</b>     | No hardwiring, only requires plug-in electrical outlet.                        |
| <b>OPERATION</b> | Simple operating panel.                                                        |
| <b>GUARANTEE</b> | Includes a three-year warranty for parts and labor.                            |

### OTHER MODELS AVAILABLE

- |                   |                                                          |
|-------------------|----------------------------------------------------------|
| <b>SC 2 DD WH</b> | Heat cycle kills lice, bedbugs, and their eggs (125°F).  |
| <b>SC 2 DD WD</b> | Drying cycle dries damp apparel and gear without damage. |

### ACCESSORIES

- |                          |                             |                                   |                                          |
|--------------------------|-----------------------------|-----------------------------------|------------------------------------------|
| <b>RR 7 7-bin Cart</b>   | <b>HC 3M 48 Helmet Cart</b> | <b>4S UC 4-shelf Utility Cart</b> | <b>4S D UC 4-shelf Deep Utility Cart</b> |
| <b>PC 2M 22 Pad Cart</b> | <b>GC Garment Cart</b>      | <b>SD 16 Shoe Dryer</b>           |                                          |