


ZONO™ SC 2 DD WD Double Door Double Deep Cabinet with Drying



On-site Assembly Required
 For recessed or side wall installation
 guides, please visit:
zonoinstallationguides.com

YOUR TRUSTED PARTNER IN DISINFECTING* & SANITIZING*

EFFECTIVE

The Patent Pending ZONO™ Cabinet disinfects and sanitizes many different surfaces, including plastics, electronics, metal, and varnished wood; and sanitizes fabrics and other porous surfaces without using liquid chemicals.

SIMPLE

The ZONO™ Cabinet is simple to set up and easy to operate. Place items onto the Integrated Mobile Carts and roll them directly into the ZONO™ Cabinet. No user assistance is needed during operation, and in 38 minutes, items are ready to use immediately, with no rinsing, wiping, or worry.

SAFETY FEATURES

Numerous safety features exist to provide protection during operation:

- Emergency stop buttons inside and outside
- Clear safety glass panel doors
- Password protected digital display panel
- Ozone sensors
- Magnetic door lock
- Ozone rated door gaskets

SUSTAINABLE

- The ZONO™ Cabinet uses four cents of electricity per cycle
- The ZONO™ Cabinet uses 1.2 ounces of distilled water per cycle

KILLS 99.9% OF COMMON VIRUSES* & BACTERIA* IN 38 MINUTES

(Tested by Certified Independent Laboratories)

- ✓ Measles
- ✓ Norovirus
- ✓ Influenza-A
- ✓ Respiratory Syncytial Virus (RSV)
- ✓ Staphylococcus aureus (Staph)
- ✓ Methicillin-Resistant Staphylococcus aureus (MRSA)
- ✓ Escherichia Coli (E. Coli)
- ✓ Streptococcus pyogenes (Strep)
- ✓ Shigella dysenteriae (Shigella)
- ✓ Salmonella enteritidis (Salmonella)
- ✓ Pseudomonas aeruginosa (Pseudomonas)

SPECIFICATIONS

- Ozone and humidity are generated in the airtight cabinet to disinfect and sanitize.
- **On-site Assembly Required:** Ships and arrives in two (2) sections that bolt together at your placement of use. Onsite caulking at the seam required.
- Drying cycle dries damp apparel and gear without damage. Heat cycle to kill bed bugs, lice, and their eggs.
- Exterior meets ASTM C1055 standards. Safe to touch during operation.
- Outer Dimensions: 80 1/2" H x 52 3/8" W x 62" D | Interior: 60" H x 48 1/2" W x 52 3/8" D.
- Capacity: 113.6 cu ft. | Weight: 496 lbs.
- Max Watts: Sanitizing Cycle 800 | Dry Cycle 3200 | Heat Cycle 3200
- No downtime between cycles.
- Requires NEMA 14-30R 240V Receptacle on Dedicated 30A 2 Phase Circuit.
- Access to the rear of the machine is required for electrical to plug into the building's receptacle.
- Proudly made in the USA in a U.S. EPA registered facility.



Use NEMA 14-30R 240V Receptacle.
 When running dry cycle, requires dedicated 30A 2 Phase Circuit. Optimum if located 36" AFF.

EASE OF USE FEATURES

ERGONOMIC

The Integrated Mobile Cart System alleviates the need for bending and lifting.

FAST

Sanitizing cycles last only 38 minutes. No delay between cycles.

DRY / HEAT

Dry and Heat cycles lasts 90 minutes. Items can be removed immediately. Cool down may be required before starting heat next cycle.

POWER

No hardwiring, only requires plug-in electrical outlet.

OPERATION

Simple operating panel.

GUARANTEE

Includes a three-year warranty for parts and labor.

OTHER MODELS AVAILABLE

SC 2 DD

Without optional drying cycle.

SC 2 DD WH

Heat cycle kills lice, bedbugs, and their eggs (125°F).

ACCESSORIES

RR 7 7-bin Cart

HC 3M 48 Helmet Cart

4S UC 4-shelf Utility Cart

4S D UC 4-shelf Deep Utility Cart

PC 2M 22 Pad Cart

GC Garment Cart

SD 16 Shoe Dryer